

Position indicator SASF-S3-B-F-A30

Part number: 8140397

FESTO



Data sheet

Feature	Value
Adjustment range of swivel angle	0 deg...180 deg
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 2
Dimensions W x L x H	Ø 40 x 43
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-25 °C...70 °C
Product weight	26 g
Type of mounting	as per VDI/VDE 3845
Housing colour	Black
Note on materials	RoHS-compliant
Spacer element material	PP
Housing material	PP High-alloy stainless steel
Material of screws	High-alloy stainless steel