

Blanking plug B-1/8-F1A

Part number: 8142289

FESTO



Data sheet

Feature	Value
Pack size	10
Conforms to standard	DIN 908
Variants	Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Product corresponds to Festo's internal product definition for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom class	Class 6 according to ISO 14644-1
Nominal tightening torque	5 Nm
Tolerance for nominal tightening torque	-20%
Product weight	7 g
Type of mounting	Internal hexagon, AF 5
Pneumatic connection 1	External thread G1/8
Note on materials	RoHS-compliant
Blanking plug material	Steel, nickel-plated
O-ring material	PA TPE-U(PUR)