

Blanking plug B-1/4-F1A

Part number: 8142290

FESTO



Data sheet

| Feature | Value |
|--|---|
| Pack size | 10 |
| Conforms to standard | DIN 908 |
| Variants | Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Product corresponds to Festo's internal product definition for use in battery production:Metals with more than 1% by mass of copper, zinc or nickel are excluded from use.The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class | Class 6 according to ISO 14644-1 |
| Nominal tightening torque | 8.5 Nm |
| Tolerance for nominal tightening torque | -20% |
| Product weight | 15 g |
| Type of mounting | Internal hexagon, AF 6 |
| Pneumatic connection 1 | External thread G1/4 |
| Note on materials | RoHS-compliant |
| Blanking plug material | Steel, nickel-plated |
| O-ring material | PA TPE-U(PUR) |