

**Double nipple**  
**NPFC-DS-G14-G12-M**  
Part number: 8142587

**FESTO**



**Data sheet**

| Feature                                           | Value                                         |
|---------------------------------------------------|-----------------------------------------------|
| Threaded fitting material                         | Brass, nickel-plated                          |
| Pack size                                         | 10                                            |
| Operating pressure                                | -0.95 bar...10 bar                            |
| Operating medium                                  | Compressed air as per ISO 8573-1:2010 [:-::-] |
| Corrosion resistance class (CRC)                  | 1 - Low corrosion stress                      |
| LABS (PWIS) conformity                            | VDMA24364-B2-L                                |
| Ambient temperature                               | -10 °C...60 °C                                |
| Nominal tightening torque, pneumatic connection 1 | 47.9 Nm                                       |
| Nominal tightening torque, pneumatic connection 2 | 9.05 Nm                                       |
| Tolerance for nominal tightening torque           | ± 20%                                         |
| Product weight                                    | 34.4 g                                        |
| Pneumatic connection 1                            | G1/2                                          |
| Pneumatic connection 2                            | G¼                                            |
| Note on materials                                 | RoHS-compliant                                |
| Seals material                                    | PVC                                           |