

Power supply unit CACN-3A-1-5-G2

Part number: 8149580

FESTO



Data sheet

Feature	Value
Width	35 mm
Height	130 mm
Length	115 mm
Mounting position	Free convection
Primary supply	1-phase
Input current	1.1 - 2.2 A
Nominal output voltage DC	24 V
Nominal output current	5 A
Input voltage range AC	100 V...240 V
Power failure buffering	100 ms
Mains frequency	45 Hz...65 Hz
Certification	c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU low voltage directive
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-40 °C...85 °C
Relative air humidity	95 %
Degree of protection	IP20
Ambient temperature	-25 °C...70 °C
Product weight	450 g
Type of mounting	With H-rail
Note on materials	RoHS-compliant