

Cable fitting
NETC-M20-PBU-T26-EX4-E
Part number: 8151587

FESTO



Data sheet

Feature	Value
Ambient temperature	-40 °C...75 °C
Degree of protection	IP66 IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
ATEX category gas	II 2G
ATEX category for dust	II 2D
Type of ignition protection for gas	Ex eb IIC Gb
Type of (ignition) protection for dust	Ex tb IIIC Db
Explosive ambient temperature	-40°C ≤ Ta ≤ +75°C
Explosion protection certification outside the EU	EPL Db (IEC-EX) EPL Gb (IEC-EX)
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX) As per EU RoHS directive
Size	M20x1.5
Cable diameter	4 mm...13 mm
Color	Blue/black
Material for cable connector	PA
Seals material	EPDM
Product weight	13 g
Pack size	1
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant