

Connection kit
DADG-AK-G8-20-50
Part number: 8152391

FESTO



Data sheet

Feature	Value
Size	20
Stroke	50 mm
Operating pressure	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque	3 Nm
Tightening torque tolerance	±10%
Max. tightening torque, pneumatic connection 1	3 Nm
Product weight	39.2 g
Pneumatic connection	G1/8
Adapter material	Epoxy resin
Seals material	FPM
Material of screws	Steel, coated