


Axial kit
EAMM-A-D80-150A
Part number: 8157273



Data sheet

Feature	Value
Nominal length	102 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	128 kgmm ²
Transferable torque	60 Nm
Product weight	3058 g
Interface code, actuator	D80
Interface code, motor in	140A 150A
Note on materials	RoHS-compliant