


Shock absorber DYEF-G8-M4-Y1F

Part number: 8160234

FESTO



Data sheet

Feature	Value
Size	M4
Stroke	1.7 mm
Cushioning	Elastic cushioning rings/pads at both ends with metallic fixed stop
Mounting position	Any
Position sensing	None
Max. impact velocity	0.8 m/s
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	1.7 mm
Max. tightening torque	0.5 Nm
Max. energy absorption per stroke	0.005 J
Product weight	4.5 g
Type of mounting	With threaded sleeve
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	High-alloy steel