


Shock absorber

DYSD-Q11-12-12-Y1F-S-Y14

Part number: 8161527

FESTO



Data sheet

Feature	Value
Size	12
Stroke	12 mm
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Max. impact velocity	1 m/s
Reset time at room temperature	0.2 s
Mode of operation	Pushing Single-acting
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Cushioning length	12 mm
Max. stop force	1000 N
Max. energy absorption per stroke	8 J
Max. energy absorption per hour	36000 J
Max. residual energy	0.05 J
Resetting force	28 N
Min. insertion force	100 N
Product weight	95 g
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Steel, galvanized
Piston rod material	High-alloy steel
Nut material	Steel, galvanized