


Pinch valve
VZQH-2H-6-GG-V4V4EPM-6
 Part number: 8187050

FESTO



Data sheet

Feature	Value
Structural design	Pinch valve
Actuation type	Manual
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	G1/4
Nominal width DN	6
Valve function	2/2, closed, monostable
Flow direction	Reversible
Medium pressure	0 MPa...0.6 MPa 0 bar...6 bar 0 psi...87 psi
Nominal pressure of fitting PN	10
Burst pressure	1.6 MPa 16 bar 232 psi
Reset method	Mechanical spring
Type of control	Direct
Medium	Compressed air as per ISO 8573-1:2010 [-:::1] Water
Max. viscosity	4000 mm ² /s
Temperature of medium	-5 °C...100 °C
Ambient temperature	-5 °C...60 °C
Storage temperature	6 °C...8 °C
Flow rate Kv	0.7 m ³ /h
On switching time	1000 ms
Switching time off	1000 ms
Note on materials	RoHS-compliant

Feature	Value
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	High-alloy stainless steel
Material number of housing	1.4408
Housing cover material	High-alloy stainless steel
Material no. housing cover	1.4404 / AISI 316L
Seals material	FPM HNBR
Shut-off element material	EPDM
Product weight	370 g
For use in the food industry	See supplementary material information