

Separator VABD-XA-12-P1

Part number: 8191736

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 12 |
| Pressure zone separation | Channel 1 |
| Pack size | 1 |
| Operating pressure | -0.1 MPa...0.7 MPa -1 bar...7 bar |
| Suitability for vacuum | yes |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -20 °C...70 °C |
| Product weight | 0.5 g |
| Type of mounting | Can be pressed in manually |
| Note on materials | RoHS-compliant |
| Seals material | HNBR |
| Housing material | PA-reinforced |