

Separator VABD-XA-12-P2

Part number: 8191737

FESTO



Data sheet

Feature	Value
Size	12
Pressure zone separation	Channels 3 and 5
Pack size	2
Operating pressure	-0.1 MPa...0.7 MPa -1 bar...7 bar
Suitability for vacuum	yes
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...70 °C
Product weight	0.5 g
Type of mounting	Can be pressed in manually
Note on materials	RoHS-compliant
Seals material	HNBR
Housing material	PA-reinforced