

# Blanking plug NPQX-P-PC12

Part number: 8191750

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Size                                     | Standard   |
| Mounting position                        | Any  |
| Pack size                                | 10   |
| Operating pressure                       | -0.1 MPa...1 MPa<br>-1 bar...10 bar<br>-14.5 psi...145 psi         |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 3 - High corrosion stress  |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -10 °C...60 °C   |
| Product weight                           | 0.8 g  |
| Type of mounting                         | With retaining clamp   |
| Note on materials                        | RoHS-compliant   |
| Blanking plug material                   | PA-reinforced  |
| O-ring material                          | HNBR   |