

Cover kit VAVC-F12-SCC-25-P

Part number: 8201223

FESTO



Data sheet

| Feature | Value |
|-------------------------------------|--|
| Nominal width DN | 25 |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Medium | Vapor Hydraulic fluid based on mineral oil Inert gas Mineral oil Water Filtered compressed air, 200 µm filter mesh Neutral liquids |
| Information on medium | Gaseous media are only permitted with inflow via valve seat. |
| Temperature of medium | 100 °C...230 °C |
| Ambient temperature | 0 °C...60 °C |
| Storage temperature | -10 °C...60 °C |
| Mounting position | Any |
| Product weight | 921 g |
| Note on materials | RoHS-compliant |
| Cover material | High-alloy stainless steel |
| Spindle seal material | PTFE |
| Seat seal material | PEEK |