

Coupling
EAMD-42-40-12-16X25-U
Part number: 8203728



Data sheet

Feature	Value
Diameter of holder 1	12 mm
Diameter of holder 2	16 mm
Size	42
Nominal length	40 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	38 kgmm ²
Transferable torque	21 Nm
Product weight	198 g
Note on materials	RoHS-compliant