

Adapter plate

OAMC-PA-G14-4

Part number: 8205196



Data sheet

Feature	Value
Material of mounting bracket	Anodized aluminum
Mounting position	Any
Structural design	Sub-base
Operating medium	Compressed air as per ISO 8573-1:2010 [:-::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque	1 Nm
Product weight	215 g
Type of mounting	Direct fastening via thread
Suction cup mounting	Internal thread G1/4
Suction cup mounting, quantity	4
Note on materials	RoHS-compliant
Seals material	NBR
Plate material	Wrought aluminum alloy, anodized