


Axial kit
EAMM-A-X22-42A
Part number: 8210057



Data sheet

Feature	Value
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transferable torque	0.95 Nm
Product weight	60 g
Interface code, actuator	X22
Interface code, motor in	42A
Note on materials	RoHS-compliant