

Length compensator VAL-3/8-80-F1A

Part number: 8210510

FESTO



Data sheet

Feature	Value
Suction cup holder height compensator	80 mm
Mounting position	Any
Structural design	Vacuum connection at top
Operating pressure	-0.95 bar...8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-:]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-10 °C...60 °C
Product weight	275 g
Type of mounting	With external thread M25x1.5
Suction cup mounting	Internal thread G3/8
Vacuum connection	Internal thread G3/8
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Aluminum
Retainer bracket material	Aluminum POM High-alloy stainless steel