


**Axial kit**  
**EAMM-A-T42-40G**  
Part number: 8217450



**Data sheet**

| Feature                  | Value                 |
|--------------------------|-----------------------|
| Nominal length           | 49 mm                 |
| Mounting position        | Any                   |
| Max. rotational speed    | 8000 rpm              |
| LABS (PWIS) conformity   | VDMA24364-B2-L        |
| Storage temperature      | -25 °C...60 °C        |
| Relative air humidity    | 0 - 95 %              |
| Degree of protection     | IP40                  |
| Ambient temperature      | -10 °C...60 °C        |
| Mass moment of inertia   | 3.2 kgmm <sup>2</sup> |
| Transferable torque      | 9.5 Nm                |
| Product weight           | 402 g                 |
| Interface code, actuator | T42                   |
| Interface code, motor in | 40G<br>40GA           |
| Note on materials        | RoHS-compliant        |