

Parallel kit
EAMM-U-87-T42-80P-114
Part number: 8223765

FESTO



Data sheet

Feature	Value
Size	87
Center-to-center distance	114 mm
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	3000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	0 °C...50 °C
Mass moment of inertia	44.2 kgmm ²
No-load driving torque	0.22 Nm
Transferable torque	3 Nm
Product weight	1067 g
Interface code, actuator	T42
Interface code, motor in	80P 80PA 80RA
Note on materials	RoHS-compliant