

Coupling
EAMC-56-58-16-22
Part number: 8224386

FESTO



Data sheet

Feature	Value
Diameter of holder 1	16 mm
Diameter of holder 2	22 mm
Size	56
Nominal length	58 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	128 kgmm ²
Transferable torque	60 Nm
Product weight	298 g
Note on materials	RoHS-compliant