


Coupling hub
EAMC-H-15-7-GB8-8
Part number: 8228650



Data sheet

Feature	Value
Diameter of holder 1	8 mm
Size	15
Nominal length	12.4 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	0.191 kgmm ²
Transferable torque	2 Nm
Product weight	4 g
Note on materials	RoHS-compliant