


On/off valve MS6-EM1-AGF

Part number: 8232876

FESTO



Data sheet

Feature	Value
Series	MS
Size	6
Structural design	Rotary gate valve
Actuation type	Manual
Exhaust air function	Without flow control option
Actuator lock	can be closed with accessories
Type of control	Direct
Valve function	3/2, bistable
Operating pressure	0 MPa...1.8 MPa 0 bar...18 bar
C value	30.8 l/sbar
b-value	0.57
Normal nominal flow rate (normalized to DIN 1343)	8700 l/min
Standard nominal flow rate 2-3	6200 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
For use in the food industry	See supplementary material information
Type of mounting	Optionally: Line installation With accessories
Mounting position	Any
Flow direction	Non-reversible
Product weight	880 g
Pneumatic connection 1	G1
Pneumatic connection 2	G1
Pneumatic connection 3	G1/2

Feature	Value
Seals material	TPE-U(PU)
Housing material	Die-cast aluminum