

Lubricator MS6-LOE-AGF-R

Part number: 8232973

FESTO



Data sheet

Feature	Value
Size	6
Series	MS
Mounting position	Vertical +/- 5°
Structural design	Proportional standard oil mist lubricator
Max. oil capacity	75 cm³
Bowl guard	Plastic bowl guard
Operating pressure	0.1 MPa...1.6 MPa 1 bar...16 bar 14.5 psi...232 psi
Minimum flow rate for lubricator function	50 l/min
Normal nominal flow rate (normalized to DIN 1343)	7200 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C...60 °C
Oil viscosity	ISO VG 32
Ambient temperature	-10 °C...60 °C
Product weight	900 g
Type of mounting	Optionally: Line installation With accessories
Pneumatic connection 1	G1
Pneumatic connection 2	G1
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum
Seals material	NBR
Housing material	Die-cast aluminum
Material of bowl	PC