


Service unit combination MSB4-1/4:I1:I3

Part number: 8233006

FESTO



Data sheet

Feature	Value
Size	4
Series	MS
Mounting position	Vertical +/- 5°
Condensate drain	Manually rotating
Structural design	Fiber filter
Max. condensate volume	19 ml
Bowl guard	Plastic bowl guard
Operating pressure	0 MPa...1.4 MPa 0 bar...14 bar 0 psi...203 psi
Max. standard flow rate	360 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [6:::4] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-10 °C...60 °C
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [5:::3]
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	400 g
Type of mounting	With accessories
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Seals material	NBR
Compressed air filter material	Borosilicate fiber
Housing material	Die-cast aluminum
Material of bowl	PC