


# Service unit combination

## MSB6-3/8:12:14

Part number: 8233037

FESTO



## Data sheet

| Feature                          | Value                                                      |
|----------------------------------|------------------------------------------------------------|
| Size                             | 6                                                          |
| Series                           | MS                                                         |
| Mounting position                | Vertical +/- 5°                                            |
| Condensate drain                 | Fully automatic                                            |
| Structural design                | Fiber filter                                               |
| Max. condensate volume           | 38 ml                                                      |
| Bowl guard                       | Plastic bowl guard                                         |
| Operating pressure               | 0.2 MPa...1.2 MPa<br>2 bar...12 bar<br>29 psi...174 psi    |
| Max. standard flow rate          | 900 l/min                                                  |
| Operating medium                 | Compressed air as per ISO 8573-1:2010 [6:::4]<br>Inert gas |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress                              |
| LABS (PWIS) conformity           | VDMA24364-B1/B2-L                                          |
| Storage temperature              | -10 °C...60 °C                                             |
| Air quality class at the output  | Compressed air as per ISO 8573-1:2010 [5:::3]              |
| Temperature of medium            | -10 °C...60 °C                                             |
| Ambient temperature              | -10 °C...60 °C                                             |
| Product weight                   | 1240 g                                                     |
| Type of mounting                 | With accessories                                           |
| Pneumatic connection 1           | G3/8                                                       |
| Pneumatic connection 2           | G3/8                                                       |
| Seals material                   | NBR                                                        |
| Compressed air filter material   | Borosilicate fiber                                         |
| Housing material                 | Die-cast aluminum                                          |
| Material of bowl                 | PC                                                         |