

Flow control/muffler GRU-1/8-B

Part number: 9516

FESTO



Data sheet

| Feature | Value |
|---|--|
| Valve function | Sound pressure flow control function |
| Selection of additional function | with muffler |
| Pneumatic connection 1 | G1/8 |
| Adjusting element | Slotted screw |
| Type of mounting | Screw-in |
| Standard flow rate 6->0 bar | 0 l/min...1000 l/min |
| Ambient temperature | -10 °C...70 °C |
| Housing material | Aluminum |
| Mounting position | Any |
| Operating pressure for entire temperature range | 0 bar...10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:::] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | -10 °C...70 °C |
| Product weight | 10 g |
| Cushioning insert material | PE |
| Material of screwed plug | Die-cast aluminum |
| Note on materials | RoHS-compliant |
| Material of adjusting screw | PA |