

Adapter
AD-1/4NPT-G1/4-I
Part number: 9625

FESTO



Data sheet

Feature	Value
Nominal width	7.95 mm
Operating pressure for entire temperature range	-0.95 bar...10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque, pneumatic connection 1	12 Nm
Max. tightening torque, pneumatic connection 2	11 Nm
Product weight	21 g
Pneumatic connection 1	external thread 1/4 NPT
Pneumatic connection 2	Internal thread G1/4
Note on materials	RoHS-compliant
Seals material	PVC
Housing material	Steel, galvanized