

Double nipple E-G3/8-3/8NPT

Part number: 9632

FESTO



Data sheet

Feature	Value
Nominal width	11.5 mm
Operating pressure for entire temperature range	-0.95 bar...10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. tightening torque, pneumatic connection 1	25 Nm
Max. tightening torque, pneumatic connection 2	22 Nm
Nominal tightening torque	38.5 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	25.5 g
Pneumatic connection 1	G3/8
Pneumatic connection 2	3/8 NPT
Note on materials	RoHS-compliant