


Short pulse valve VLK-3-PK-3

Part number: 9639



Data sheet

Feature	Value
Nominal width	2.5 mm
Operating pressure	2.5 bar...8 bar
Standard nominal flow rate	90 l/min
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Product weight	170 g
Type of mounting	On mounting frame
Seals material	TPE-U(PU)
Housing material	Die-cast zinc