

Pressure gauge OH-10

Part number: 9791

FESTO



Data sheet

Feature	Value
Operating pressure	0.14 MPa...0.8 MPa 1.4 bar...8 bar 20.3 psi...116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...80 °C
Product weight	4 g
Pneumatic connection	Barbed fitting PK-3
Note on materials	RoHS-compliant