

Indicator de presiune OH-8-GN

Numar piesa: 10089

FESTO



Fisa de date

Caracteristica	Valoare
Presiune de lucru	-0.1 MPa...0.8 MPa -1 bar...8 bar -14.5 psi...116 psi
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Nota referitoare la mediul de lucru/comanda	Posibilitatea operarii cu ulei (necesar pentru operare ulterioara)
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Conexiune pneumatica	Niplu de conectare PK-3
Nota privind materialele	Conform RoHS