

# Indicator de presiune OH-8-BL

Numar piesa: 10090

FESTO



## Fisa de date

| Caracteristica                              | Valoare                                                            |
|---------------------------------------------|--------------------------------------------------------------------|
| Presiune de lucru                           | -0.1 MPa...0.8 MPa<br>-1 bar...8 bar<br>-14.5 psi...116 psi        |
| Protectie la explozie                       | Zona 1 (ATEX)<br>Zona 2 (ATEX)<br>Zona 21 (ATEX)<br>Zona 22 (ATEX) |
| Mediu de operare                            | Aer comprimat conform ISO 8573-1:2010 [7:-:-]                      |
| Nota referitoare la mediul de lucru/comanda | Posibilitatea operarii cu ulei (necesar pentru operare ulterioara) |
| Conformitatea LABS                          | VDMA24364-B1/B2-L                                                  |
| Temperatura ambianta                        | -10 °C...60 °C                                                     |
| Conexiune pneumatica                        | Niplu de conectare PK-3                                            |
| Nota privind materialele                    | Conform RoHS                                                       |