


Amortizor de soc DYSR-8-8-Y5

Numar piesa: 1138641

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	8
Cursa	8 mm
Amortizare	reglabil
Pozitie de instalare	orice
Detectarea pozitiei	fara
Viteza max. de impact	3 m/s
Timp de resetare la temperatura camerei	0.2 s
Timp de resetare la temperatura ambientala minima	3 s
Mod de functionare	cu apasare cu simpla actiune
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-10 °C...80 °C
Lungime de amortizare	8 mm
Forta max. de ridicare	400 N
Consumul max. de energie pe cursa	4 J
Consum max. de energie pe ora	24000 J
Energie reziduala max.	0.01 J
Forta de restabilire	1.8 N
Forta minima de insertie	18 N
Greutate produs	60 g
Interval de masa	40 kg
Tipul de montare	cu piulita de blocare
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material carcasa	Otel aliaj inalt
Material tija de piston	otel aliaj inalt