


# Amortizor de soc DYSR-12-12-Y5-T

Numar piesa: 1138643

FESTO



## Fisa de date

Caracteristica	Valoare
Dimensiune	12
Cursa	12 mm
Amortizare	reglabil
Pozitie de instalare	orice
Detectarea pozitiei	fara
Viteza max. de impact	3 m/s
Timp de resetare la temperatura camerei	0.2 s
Timp de resetare la temperatura ambientala minima	1 s
Mod de functionare	cu apasare cu simpla actiune
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambienta	-10 °C...80 °C
Lungime de amortizare	12 mm
Fora max. de ridicare	900 N
Consumul max. de energie pe cursa	10.8 J
Consum max. de energie pe ora	60000 J
Energie reziduala max.	0.05 J
Fora de restabilire	4.5 N
Fora minima de insertie	38 N
Greutate produs	120 g
Interval de masa	90 kg
Tipul de montare	cu piulita de blocare
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material carcasa	Otel galvanizat
Material tija de piston	otel aliaj inalt