


Flansa motor EAMF-A-28D-40A

Numar piesa: 1199144

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-10 °C...60 °C
Greutate produs	48 g
Codul interfetei motor In	40A
Cod de interfata carcasa de cuplare	28D
Nota privind materialele	Conform RoHS