

Amortizor de zgomot AMTE-M-LH-G18

Numar piesa: 1205860

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Unitate de ambalare	20
Presiune de lucru	0 MPa...1 MPa 0 bar...10 bar
Debit in raport cu atmosfera	1735 l/min
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Nivel de presiune acustica	76 dB(A)
Temperatura ambianta	-40 °C...80 °C
Greutate produs	7.5 g
Conexiune pneumatica	G1/8
Material insertie amortizor de zgomot	Bronz
Material pivot de insurubare	Alama
Nota privind materialele	Conform RoHS