

Inel de centrare EAML-80-6-80

Numar piesa: 1209006

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	38 mm
Diametru de montare 2	80 mm
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-10 °C...60 °C
Greutate produs	23 g
Cod de interfata actuator	M80
Cod de interfata carcasa de cuplare	80A
Nota privind materialele	Conform RoHS