

Bobina MSN1G-24DC-OD

Numar piesa: 123060

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Ora min. de preluare	10 ms
Ciclu de lucru	100%
Caracteristici bobina	24 V CC: 2,5 W
Fluctuatii de tensiune admise	-15 % / +10 %
Autorizare	c UL us - recunoscut (OL)
Conformitatea LABS	VDMA24364-C1-L
Temperatura medie	-10 °C...50 °C
Tip de protectie	IP65
Temperatura ambianta	-10 °C...50 °C
Greutate produs	80 g
Conector electric	3 pini Forma A conform DIN EN 175301-803
Tipul de montare	prinsa cu clema cu clema de retinere cu accesorii
Material carcasa	PA
Material contacte de cuplare	Otel
Material infasurare	Cupru