

**Cuplaj**  
**EAMC-30-35-6-11**  
Numar piesa: 123843

**FESTO**



**Fisa de date**

| Caracteristica               | Valoare               |
|------------------------------|-----------------------|
| Diametrul de montare 1       | 6 mm                  |
| Diametru de montare 2        | 11 mm                 |
| Dimensiune                   | 30                    |
| Lungime nominala             | 35 mm                 |
| Pozitie de instalare         | orice                 |
| Turatie max.                 | 8000 1/min            |
| Conformitatea LABS           | VDMA24364-B2-L        |
| Temperatura de depozitare    | -25 °C...60 °C        |
| Umiditate relativa           | 0 - 95 %              |
| Temperatura ambianta         | -25 °C...60 °C        |
| Momentul de inertie al masei | 6.1 kgmm <sup>2</sup> |
| Cuplu transmisibil           | 7.5 Nm                |
| Greutate produs              | 45 g                  |
| Nota privind materialele     | Conform RoHS          |