

Cuplaj
EAMC-40-66-15-20
Numar piesa: 123845

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	15 mm
Diametru de montare 2	20 mm
Dimensiune	40
Lungime nominala	66 mm
Pozitie de instalare	orice
Turatie max.	6500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	42.3 kgmm ²
Cuplu transmisibil	21 Nm
Greutate produs	139 g
Nota privind materialele	Conform RoHS