

Conector indicator MFLZ-24DC/AC

Numar piesa: 12610

FESTO



Fisa de date

Caracteristica	Valoare
Greutate produs	14 g
Conector electric	Forma B conform standardului industrial (11 mm)
Tensiune nominala de functionare CC	24 V
Tensiunea nominala de functionare CA	24 V
Frecventa retelei	0 Hz...60 Hz
Fluctuatii de tensiune admise	+/- 15 %
Tip de protectie	IP65 conform IEC 60529
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	ranforsat cu PA6