

Conector indicator MCL

Numar piesa: 12611

FESTO



Fisa de date

Caracteristica	Valoare
Greutate produs	13 g
Conector electric	Forma A Stecker conform DIN EN 175301-803
Tensiune nominala de functionare CC	24 V
Tensiunea nominala de functionare CA	24 V
Frecventa retelei	0 Hz...60 Hz
Fluctuatii de tensiune admise	+/- 15 %
Tip de protectie	IP65 conform IEC 60529
Temperatura ambianta	-20 °C...60 °C
Conformitatea LABS	VDMA24364-B2-L
Material carcasa	ranforsat cu PA6