

Ventuza vacuum VASB-15-1/8-PUR-B

Numar piesa: 1395671

FESTO



Fisa de date

Caracteristica	Valoare
Ventuza de compensare a inaltimii	5.6 mm
Latimea nominala	3 mm
Diametrul ventuzei	15 mm
Volum de aspiratie	0.83 cm ³
Diametru de aspiratie eficient	12.4 mm
Pozitie de conectare	sus
Pozitie de instalare	orice
Forma de ventuza	burduf rotund de 1,5 ori
Presiune de lucru	-0.095 MPa...0 MPa -0.95 bar...0 bar -13.775 psi...0 psi
Presiunea nominala de functionare	-0.07 MPa -0.7 bar -10.15 psi
Mediu de operare	aer atmosferic conform ISO 8573-1:2010 [7::-]
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-A1-L
Temperatura ambianta	-20 °C...60 °C
Fora de mentinere la presiune de lucru nominala	8.5 N
Greutate produs	11 g
Tipul de montare	prin racordul de vid
Racord de vacuum	G1/8
Culoare	albastru
Duritate Shore	60 +/- 5
Material pivot de insurubare	Alama
Nota privind materialele	Conform RoHS
Material ventuze	PUR