

# Ventuza vacuum VASB-30-1/8-PUR-B

Numar piesa: 1395690

FESTO



## Fisa de date

| Caracteristica                                  | Valoare  |
|---|--|
| Ventuza de compensare a inaltimii               | 13.9 mm  |
| Latimea nominala                                | 3 mm   |
| Diametrul ventuzei                              | 30 mm  |
| Volum de aspiratie                              | 6.18 cm <sup>3</sup>   |
| Diametru de aspiratie eficient                  | 24.8 mm  |
| Pozitie de conectare                            | sus  |
| Pozitie de instalare                            | orice  |
| Forma de ventuza                                | burduf rotund de 1,5 ori                                       |
| Presiune de lucru                               | -0.095 MPa...0 MPa<br>-0.95 bar...0 bar<br>-13.775 psi...0 psi |
| Presiunea nominala de functionare               | -0.07 MPa<br>-0.7 bar<br>-10.15 psi                            |
| Mediu de operare                                | aer atmosferic conform ISO 8573-1:2010 [7::-]                  |
| Clasa de rezistenta la coroziune KBK            | 2 - Solicitare moderata din cauza coroziunii                   |
| Conformitatea LABS                              | VDMA24364-A1-L   |
| Temperatura ambianta                            | -20 °C...60 °C   |
| Fora de mentinere la presiune de lucru nominala | 34 N   |
| Greutate produs                                 | 14 g   |
| Tipul de montare                                | prin racordul de vid   |
| Racord de vacuum                                | G1/8   |
| Culoare   | albastru   |
| Duritate Shore                                  | 60 +/- 5   |
| Material pivot de insurubare                    | Alama  |
| Nota privind materialele                        | Conform RoHS   |
| Material ventuze                                | PUR  |