

# Set paralel EAMM-U-60-D40-42B/C-91-S1

Numar piesa: 1430735

FESTO



## Fisa de date

| Caracteristica               | Valoare            |
|------------------------------|--------------------|
| Dimensiune                   | 60                 |
| Pozitie de instalare         | orice              |
| Raportul de transmisie       | 1:1                |
| Turatie max.                 | 6000 1/min         |
| Conformitatea LABS           | VDMA24364 zona III |
| Temperatura de depozitare    | -25 °C...60 °C     |
| Umiditate relativa           | 0 - 95 %           |
| Tip de protectie             | IP65               |
| Temperatura ambianta         | -10 °C...60 °C     |
| Momentul de inertie al masei | 26.7 000065        |
| Cuplu de antrenare in gol    | 0.07 Nm            |
| Cuplu transmisibil           | 3 Nm               |
| Greutate produs              | 1130 g             |
| Cod de interfata actuator    | D40B               |
| Codul interfetei motor In    | 42B<br>42C         |
| Nota privind materialele     | Conform RoHS       |