

Cuplaj
EAMD-28-22-14-10X12
Numar piesa: 1453861

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	14 mm
Diametru de montare 2	10 mm
Dimensiune	28
Lungime nominala	22 mm
Pozitie de instalare	orice
Turatie max.	8000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	3.5 kgmm ²
Cuplu transmisibil	9 Nm
Greutate produs	43 g
Nota privind materialele	Conform RoHS