

**Cuplaj**  
**EAMC-42-50-10-12**  
Numar piesa: 1455666

**FESTO**



**Fisa de date**

| Caracteristica               | Valoare                |
|------------------------------|------------------------|
| Diametrul de montare 1       | 10 mm                  |
| Diametru de montare 2        | 12 mm                  |
| Dimensiune                   | 42                     |
| Lungime nominala             | 50 mm                  |
| Pozitie de instalare         | orice                  |
| Turatie max.                 | 6000 1/min             |
| Conformitatea LABS           | VDMA24364-B2-L         |
| Temperatura de depozitare    | -25 °C...60 °C         |
| Umiditate relativa           | 0 - 95 %               |
| Temperatura ambianta         | -25 °C...60 °C         |
| Momentul de inertie al masei | 34.8 kgmm <sup>2</sup> |
| Cuplu transmisibil           | 17 Nm                  |
| Greutate produs              | 145 g                  |
| Nota privind materialele     | Conform RoHS           |