

Set axial EAMM-A-R27-40G

Numar piesa: 1456622

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	32 mm
Pozitie de instalare	orice
Turatie max.	10000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	0.445 kgmm ²
Cuplu transmisibil	2 Nm
Greutate produs	240 g
Cod de interfata actuator	R27
Codul interfetei motor In	40G
Nota privind materialele	Conform RoHS